


Type J Glassfibre IsolÃ© Flat Pair Câble / Fil avec overbraid en acier inoxydable (BS)

Type J, 14/0.2mm
SSOB PTFE



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Type J Glassfibre Isolé Flat Pair Câble / Fil avec overbraid en acier inoxydable (BS)

L'image est pour l'illustration de codage de couleur seulement

Le prix est par metre - s'il vous plaît ajouter la quantité nécessaire pour le panier. Il ne reste plus que 336 metres en stock

Construction isolée de paires plates de Glassfibre, conducteurs posés a plat, Glassfibre isolé avec veste Glassfibre, silicone vernis tout au long de l'acier inoxydable overbraid pour une protection supplémentaire et une force mécanique. Bonne résistance a la température mais ne convient pas lorsque les fluides sont présents.

Spécifications
Specifications

Product Code	WJ-247-D
General Description	Good temperature range but will not prevent ingress of fluids. Fairly flexible but does not provide good mechanical protection.
Cable Length	Priced per metre
Cable Type	SSOB PTFE
Core / Strands	14/0.2mm
Outer Colour	Black
+ Colour	Yellow
- Colour	Blue
Insulation Material	Glassfibre insulated extension cable with stainless steel overbraiding
Max. Temperature	+350°C (short periods up to 400°C)
Min. Temperature	-60°C
+ Conductor	Iron
- Conductor	Constantan



LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Standards Met	BS
Thermocouple Type	J
Tolerance	Class 2